

87045 LIMOGES Cedex

Phone number: (+33) 05 55 06 87 87 - Fax: (+33) 05 55 06 88 88

Archimod 40 kVA

3 104 53



INDEX		ge
1.	General specifications	.1
2.	Technical specifications	.2

1. GENERAL SPECIFICATIONS

The Legrand Archimod, model 40000VA, is an UPS on line double conversion with PWM Hi-Frequency technology. It has passing trough neutral and Modular Architecture with the possibility to have N+X redundancy. The nominal power is 40.000 VA - 36.000 W. Batteries are lead acid, sealed, free maintenance, valve regulated, and arranged, inside the UPS or external battery cabinet, in dedicated Drawers, in order to guarantee compact dimensions reducing weights and DC voltage level.

1.1 Modularity

The UPS Archimod 40000VA has modular architecture, it is composed by identical modules which work in parallel. Modules are:

- · Power Modules 6700VA;
- · Battery Drawers of seven batteries (9Ah).

These modules are installed inside the UPS and have identical

Power Modules are composed by the following circuits:

- Rectifier/PFC
- Inverter
- Battery Charger
- · Command Logic circuit
- Automatic By-pass

Battery drawers contain 7 batteries, and are easy to be move and replace.

1.2 Adaptabilty

The UPS can be easily configured on site, by the user, to work as three-phase or single phase either in input than output.

1.3 Scalability

The modularity of ARCHIMOD UPS allows to execute Power and Autonomy upgrade. Thanks to the intelligent Plug N' Play connection, no HW and SW settings are needed to increase or decrease the power or the autonomy.

The modularity of the UPS allows the N+X redundant configurations. The Redundancy is achieved using more modules than needed, modules will run in "load sharing".

The UPS Archimod 40000VA is three-phase input and output, the architecture is distributed parallel architecture in each phase (there are more modules in the same phase).

In case of redundant configuration, whenever one module fails, the other modules in the same phase will guarantee the Energy supply and protection to the load.

The available power in each phase will be always the sum of the power of the modules installed in that phase.

1.6 Hot-plug

The UPS Archimod 40000VA The power modules are independently controlled by 2 Command Tunnel. Each Command Tunnel controls, three power modules. It is possible to turn off only one command tunnel and install or replace modules inside of it, when the other tunnel is still running.

This allows the service on a part of the UPS without turn off the complete system, losing only the power of the tunnel in maintenance. In case of redundancy or scalability, the load is protected by the UPS also during the replace or upgrade of power modules.

1.7 By-pass

In each Power Module there is a static By-pass system which, in case of overload or other anomaly, automatically transfer the load to the

The UPS has embedded the manual bypass for service and maintenance and it is possible to connect a dedicated bypass input line.

Control and Monitoring:

A dedicated software of remote monitoring and management, installed on a PC connected to the UPS, allows to check and set all working parameters of Archimod (the same functions available on the UPS control panel) and, furthermore, to schedule and program computer remote shutdown.

Optional software (UPS SuperviSor) or Net Interface card (CS121 SK) allow the multi server shutdown and UPS remote control on the LAN.

Archimod is controlled by a main microprocessor which works together with microprocessors in each power modules; By display is possible to check all measurements, working parameters and status of the system.

Here follow the measurements and working parameters available on the display:

Input

Current:

- RMS value
- Peak value
- Crest Factor Voltage:
- Ph-N RMS value
- Ph-Ph RMS value
- Bypass Line Voltage

Power:

- Nominal (VA)
- Active (W) Power Factor

Frequency

Output

- Current: RMS value
- · Peak value
- · Crest Factor
- Voltage:
- · Ph-N RMS value · Ph-Ph RMS value

Power:

- Nominal (VA)
- · Active (W)

Power Factor Frequency

Technical sheet: UPS-LGR-0040/GB Last update: 01/09/2012 01/09/2012

1. GENERAL SPECIFICATIONS (continue)

Batteries

- Voltage
- Capacity
- Current
- · History data
- Residual Capacity
- Charging status

Misc.

- Internal Temperature
- · Fan Speed
- HV DC BUS Voltage

The UPS allows also the following settings by display

Output

- Voltage
- Frequency
- Phases configuration

Inpu

- Enable freq. synchronizing (PLL)
- Extended synchronizing range (Extended PLL)

Events

Alarms

DATA LOG.

· Overheats

Overloads

· By-pass intervention

Battery interventions

(info, warning, critical)

· Total discharge

- **BY-PASS**
- Enabling
- Forced
- · DIP Speed
- ECO Mode

Batteries

- · Start up on Battery
- · Threshold value
- · Auto restart
- · Max Time on battery

The UPS Archimod has the CE Mark accordingly with the EU Directives 73/23, 93/68, 89/336, 92/31, 93/68 and it comply with following standards:

- EN 62040-1 "General rules for electric safety"
- EN 62040-2 "Electromagnetic compatibility and immunity (EMC)"
- EN 62040-3 "Performances and testing rules"

2. TECHNICAL SPECIFICATIONS

General Specifications		
UPS Topology	On line double conversion VFI SS 111	
Architecture of the UPS	Modular, scalable, redundant based on 6.7kVA Power Modules	
In/Out phase Configuration	Three phase-Three phase (also configurable single-phase)	
Neutral	Neutral Passing through	
Output wave form on mains run	Sinusoidal	
Output wave form on battery run	Sinusoidal	
Bypass type	Static and electro-mechanic	
Transfer time	Zero	

Input		
Nominal Voltage	400 V three phase / 230V single phase	
Voltage range	-20% +15%	
Frequency	50 Hz o 60Hz (autosensing)	
THDI _{in}	< 3% al 100% of nominal load	
Power Factor	> 0.99 from 50% to 100% of nominal load	

Output with mains (AC-AC)		
Nominal voltage	400 V three phase / 230V single phase	
Nominal power	40.000 VA	
Active power	36.000 W	
Voltage variation (static)	± 1%	
Voltage variation (dynamic 0-100%; 100-0%)	± 1%	
THDv on nominal power (linear load)	< 0,5 %	
THDv on nominal power (not linear load P.F.=0,7)	< 1 %	
Frequency	50 Hz o 60 Hz (autosensing or selectable)	
Frequency tolerance	Synchronized with input frequency or ± 1% free run	
Current Crest Factor	3:1 accordingly with IEC 62040-3	
Overload capability: • 5 min • 30 sec	125% load rate with no bypass intervention 150% load rate with no bypass intervention	

Output in hottom: Dun (DC AC)		
Output in battery Run (DC-AC)		
Nominal voltage	400 V three phase / 230V single phase	
Nominal power	40.000 VA	
Active power	36.000 W	
Voltage variation (static)	± 1%	
Voltage variation (dynamic 0-100%; 100-0%)	± 1%	
THDv on nominal power (linear load)	< 0,5 %	
THDv on nominal power (not linear load P.F.=0,7)	< 1 %	
Frequency	50 Hz o 60 Hz (autosensing or selectable)	
Frequency tolerance	± 1% free run	
Current Crest Factor	3:1 accordingly with IEC 62 040-3	
Overload capability: • 5 min • 30 sec	125% load rate with no bypass intervention 150% load rate with no bypass intervention	

Battery	
Туре	Lead Acid, sealed, free maintenance VRLA
Unit Capacity	9 Ah (12V)
Nominal UPS Battery Voltage	252 Volt DC
Battery charger type	PWM hi efficiency, one in each power module
Charging Cycle	Intelligent with boost charge and advanced management
Max Charging Current	2,5 A each power module

Environmental specs		
Noise level @ 1m	52 dBA	
Working temperature range	from 0°C to +40°C	
Stock temperature range	from -20°C to +50°C (excluded batteries)	
Humidity range	20-80% not condensing	
Protection degree	IP21	

Mechanical an Miscellaneous		
Net Weight without batteries 1	240 kg	
Dimensions (W×HxD) ²	1 x (570 x 2170 x 912) (mm)	
Colour	RAL 7016	
Technology rectifier/booster/inverter	MOSFET/IGBT	
Communication Interface (for each command tunnel)	2 serial port RS232, 1 logic level port, 5 Dry contacts port	
Input/Output connections	3P + N + PE	
Number of Command Tunnels	2	
Number of Installed Power Modules	6 of 6700 VA	
Standards	EN 62040-1, EN 62040-2, EN 62040-3	

¹ The weigh depends by the number of the installed batteries accordingly with the required autonomy.

Last update: 01/09/2012

La legrand

² The battery cabient dimension can change depending battery set accordingly with the required autonomy.