







KEORS SINGLE PHASE **UPS DESIGNED** FOR INDUSTRIAL **APPLICATIONS**

Compact and robust, Keor S is the perfect UPS to protect and supply loads in the industrial fields.

Power Range From 3 KVA up to 10KVA

Power factor 0,9

High Efficiency up to 94%

Built in paralleling feature up to 4 units

Built in Back Feed Protection

Protection Degree IP31

Long back up time availability

Integrated maintenance bypass

Integrated internal isolation transformer option



Remote control & Monitoring Supervision



Easy to move

User friendly Display

KEOR S ONLINE single phase

The integrated maintenance bypass simplifies the maintenance operations, increases the service continuity and helps to reduce the complexity of the installations.

Easy access to circuit breakers, INPUT/OUTPUT terminals, maintenance bypass and communication port



on line UPS compact and easy to move





DISPLAY

All parameters & status of the ups is available on the display:

- Input voltage
- Input frequency
- Output voltage
- Output frequency
- % load
- Battery voltage
- Internal temperature

	-220°
LINE – UPS – LOAD	50,0 "
LINE – UPS – LOAD	220°
LINE – UPS – LOAD	50.0 "
LINE - UPS - LOAD	80.
	80.
LINE – UPS – LOAD	30



ADDITIONAL BATTERY CHARGER

Thanks to the external additional charger we can propose short recharge times also on the long back up time configurations.



PARALLEL REDUNDANT APPLICATIONS UP TO 4 UNITS

UPS built in paralleling function and ready to actuate on site easily up to 4 units. This architecture eliminates risk of single point of failure.





KEOR S Conventional UPS - Single-phase On-line double conversion VFI





3 101 20

3 107 41

Pack	Cat. Nos.	SINGLE-PHASE	UPS		
		NOMINAL POWER VA	ACTIVE POWER W	BACKUP TIME (MIN.)	NET WEIGHT (kg)
	3 101 21	3000	2400	8	53
	3 101 22	3000	2400	27	75
	3 101 23	3000	2400	50	97
	3 101 28	6000	5400	55	106
	3 101 31	10000	9000	10	114

SINGLE-PHASE UPS WITH ISOLATION TRANSFORMER

	NOMINAL POWER VA	ACTIVE POWER W	BACKUP TIME (MIN.)	NET WEIGHT (kg)
3 101 25	3000	2400	8	85
3 101 29	6000	5400	0	100
3 101 35	10000	9000	0	126

BATTERY CABINET DESC RIPTION

3 107 40	Empty battery cabinet
3 107 41	Battery cabinet with 2x6x12 Ah (for KEOR S 3000)
3 107 42	Battery cabinet with 3x6x12 Ah (for KEOR S 3000)
3 107 43	Battery cabinet with 6x6x12 Ah (for KEOR S 3000)
3 107 44	Battery cabinet with 20x12 Ah (for KEOR S 6000-10000)
3 107 45	Battery cabinet with 2x20x12 Ah (for KEOR S 6000-10000)

ACCESSORIES

	DESCRIPCIÓN
3 109 61	Battery charger for additional battery cabinet (for 3 107 41 - 3 107 42 - 3 107 43)
3 109 54	Battery charger for additional battery cabinet (for 3 107 44 - 3 107 45)

UPS WITH INTERNAL BATTERIES BACKUP TIME UP TO 42 MIN FOR 3 KVA



UPS FOR LONG AUTONOMY WITH ADDITIONAL BATTERY CABINET



UPS WITH ISOLATION TRANSFORMER BUILT IN



La legrand®

KEOR S Conventional UPS - Single-phase On-line double conversion VFI

Model.		KEOR S 3kVA	KEOR S 6kVA	KEOR S 10kVA	
General char	acteristics				
	Nominal power (VA)	3000	6000	10000	
	Active power (W)	2400	5400	9000	
	Technology	On-line double conversion VFI-SS-111		1	
	Waveform	Sinusoidal			
	Architecture	conventional UPS			
Input charact	teristics				
	Input voltage		220V-230V-240V		
	Input frequency	45-55	45-	65	
	Input voltage range	160V-288V	180V-	280V	
	THD of input current		6%		
	Input power factor		> 0,99		
Output chara	cteristics				
	Output voltage	220V/230V/240V			
	Output frequency (nominal)	50/60	0 /60 Hz Adjustable from Front Panel +/- 0,05%		
	Crest factor		3:1		
	THD of output voltage	< 1,5%	< 1,5% with linear load < 3% with non-linear load		
	Permissible overload	10 seconds at 125%-150% 30 seconds at 106%-120%	120 seconds at 100%-120% 30 seconds at 121%-150%		
	Efficiency in Eco mode		98%		
	Bypass	Automatic bypass and manual maintenance bypass			
Batteries					
	Backup time extension		Yes		
	Battery type		VRLA - AGM		
Communicati	ion and management				
	LCD Display	Available			
	Communication Ports	1 RS23	2 serial ports, modbus and SNMP o	ptional	
	Remote Management	Available			
Physical char	racteristics				
	Dimensions H x W x D (mm)		716 x 275 x 776		
	Dimensions battery cabinet H x W x D (mm)		716 x 275 x 776		
Ambient cond	ditions				
	Operating temperature (°C)		0÷40		
	Relative humidity (%)	20÷80 non condensing			
	Protection index		IP31		
	Noise at 1 m (dBA)		< 50		
Compliance					
	Reference product standards	E	N 62040-1, EN 62040-2, EN 62040-3	3	

 World Headquarters and International Department

 87045 Limoges Cedex - France

 ☎ : + 33 [0] 5 55 06 87 87

 Fax : + 33 [0] 5 55 06 74 55

In accordance with its policy of continuous improvement, the Company reserves the right to change specifications and designs without notice. All illustrations, descriptions, dimensions and weights in this catalogue are for guidance and cannot be held binding on the Company.