

ARCHIMOD HE 480 kVA

310476 + 310477 (empty cabinet ARCHIMOD HE 480 72 slot)
3 108 73 Power module 6,7 kW



INDEX	Page
1. General specifications	1
2. Technical specifications	2

1. GENERAL SPECIFICATIONS

The Legrand **ARCHIMOD HE 480**, is an high efficiency UPS on line double conversion with PWM Hi-Frequency technology. It has passing trough neutral and Modular Architecture with the possibility to have N+X redundancy. The nominal power is 480 kVA – 480 kW.

1.1 Modularity

The **ARCHIMOD HE 480** UPS has an innovative modular architecture called GPA (Granular Parallel Architecture), it means that it's composed by identical modules (6,7kW single phase power module) that, working in parallel, form the power section of the UPS. Each power module can be considered a complete single phase UPS who works in parallel with the others in order to supply the required power. The power module can be divided in the following functional blocs:

- Rectifier/PFC
- Inverter
- Battery Charger
- Command Logic circuit
- Automatic By-pass

It's possible to reach different power and redundancy levels according to the number of installed power module.

1.2 Scalability

The cabinet is designed to accept different number of power modules, this allows to create a huge range of configurations. It's possible to increase power directly on site easily, without changing settings nor adjustments. This operation can be lead without using any kind special equipment.

1.3 Redundancy

You can easily set up the **ARCHIMOD HE 480** as a N+X power redundant system. It will be enough defined how many 6,7kW power modules must be installed inside the cabinet. We can reach redundancy thanks to the load sharing, the overall load is equally shared between the power modules and in case of failure the still-working modules will back up the faulty one.

1.4 Architecture

The **ARCHIMOD HE 480** UPS has three phase input and output and it's possible manage the output phases in independent way thank to the granular parallel architecture (GPA). The nominal power available is determinate by the sum of the power module per phase. For this reason the UPS is able, if properly sized, to supply the load in case of failure or replacement of one or more power modules.

1.5 Hot-Swap

The power modules of the **ARCHIMOD HE 480** are supervised and managed by 4 independent control board which operate in parallel. Each control board is able to manage up to 18 power modules. This architecture allows to enable a single control board and consequently only the power modules managed for the replacement without switch off the others. In case of redundant or upgradable configuration the service technician can operate on the UPS which continues to guarantee high quality energy and protection to the load.

1.6 By-pass

Each power module has an independent automatic bypass system that switch the load on the input line in case of overload, over temperature, inverter failures, and any kind of anomalies. The UPS is equipped as standard with the Manual Bypass, placed in the front side of the cabinet.

1.7 Dual input

On the front side of **ARCHIMOD HE 480** there are 2 input switches, one for the main and one for the auxiliary line. These two switches are bridged by default but the connection can be easily removed obtaining two independent input lines during installation or commissioning.

1.8 Batteries

Batteries are lead-acid, sealed, free maintenance, valve regulated and arranged, inside the external battery cabinet; the battery strings are composed by 21 battery blocks. The UPS can manage four independent battery set in order to have full decentralised modularity also on batteries.

1.9 Communication and user interface

A dedicated software of remote monitoring and management, installed on a PC connected to the UPS, allows to check and set all working parameters of **ARCHIMOD HE 480** (the same functions available on the UPS control panel) and, furthermore, to schedule and program computer remote shutdown (compatible with Windows and Linux).

Optional software (UPS Management Software) and Net Interface card (CS141SK) allow the multi server shutdown and UPS remote control on the LAN.

ARCHIMOD HE 480 is controlled by 4 microprocessors which work together with the microprocessors embedded in each power modules; By the redundant displays is possible to check all measurements, working parameters and status of the system.

Here below the measurements and working parameters available on the display:

Input	Power:
Current:	• Nominal (VA)
• RMS value	• Active (W)
• Peak value	Power Factor
• Crest Factor	Frequency
Voltage:	
• Ph-N RMS value	
• Ph-Ph RMS value	
• Bypass Line Voltage	

All the measurements and the working parameters are also available on 2 different Net Interface Cards (SNMP) board. On the front side of **ARCHIMOD HE 480** are available also:

- 2x 5 Dry contacts
- 2x RS232 port for service
- 1x logic level port

1. GENERAL SPECIFICATIONS *(continue)*

Output

Current:

- RMS value
- Peak value
- Crest Factor

Voltage:

- Ph-N RMS value
- Ph-Ph RMS value

Power:

- Nominal (VA)
- Active (W)

Power Factor

Frequency

Batteries

- Voltage
- Capacity
- Current
- History data
- Residual Capacity
- Charging status

Misc.

- Internal Temperature
- Fan Speed
- HV DC BUS Voltage

DATA LOG.

- By-pass intervention
- Overheats
- Overloads
- Battery interventions
- Total discharge
- Events (info, warning, critical)
- Alarms

The UPS allows also the following settings by **display**:

Output

- Voltage
- Frequency
- Phases configuration

BY-PASS

- Enabling
- Forced
- DIP Speed
- ECO Mode

Input

- Enable freq. synchronizing (PLL)
- Extended synchronizing range (Extended PLL)

Batteries

- Start up on Battery
- Threshold value
- Auto restart
- Max Time on battery

The UPS **ARCHIMOD HE 480** has the CE Mark accordingly with the EU Directives 2006/95, 2004/108 and it comply with following standards:

- EN 62040-1 "General rules for electric safety"
- EN 62040-2 "Electromagnetic compatibility and immunity (EMC)"
- EN 62040-3 "Performances and testing rules"

2. TECHNICAL SPECIFICATIONS

General Specifications	
UPS Topology	On line double conversion VFI SS 111
Architecture of the UPS	Modular, scalable, redundant based on 6.7kW Power Modules
In/Out phase Configuration	Three phase-Three phase
Neutral	Neutral Passing through
Output wave form on mains run	Sinusoidal
Output wave form on battery run	Sinusoidal
Bypass type	Static, electro-mechanic and maintenance bypass
Transfer time	Zero

Input	
Nominal Voltage	380, 400, 415 3ph+N+PE
Voltage range	-20% +15%
Frequency	45 Hz o 65Hz (autosensing)
THDI _{in}	< 3%
Power Factor	> 0.99

Output with mains (AC-AC)	
Nominal voltage	380, 400, 415 3ph+N+PE
Nominal power	480 kVA
Active power	480 kW
Efficiency	up to 96%
Voltage variation (static)	± 1%
Voltage variation (dynamic 0-100%; 100-0%)	± 1%
THDv on nominal power (linear load)	< 0,5 %
THDv on nominal power (not linear load PF=1)	< 1 %
Frequency	50 Hz o 60Hz
Frequency tolerance	Synchronized with input frequency adjustable range from +/- 1% to +/- 14% or ± 1% free run
Current Crest Factor	3:1 accordingly with IEC 62040-3
Overload capability:	
• 10 min	115% load rate with no bypass intervention
• 60 sec	135% load rate with no bypass intervention

Output in battery Run (DC-AC)	
Nominal voltage	380, 400, 415 3ph+N+PE
Nominal power	480 kVA
Active power	480 kW
Voltage variation (static)	± 1%
Voltage variation (dynamic 0-100%; 100-0%)	± 1%
THDv on nominal power (linear load)	< 0,5 %
THDv on nominal power (not linear load)	< 1 %
Frequency	50 Hz o 60Hz (autosensing)
Frequency tolerance	± 1% free run
Current Crest Factor	3:1 accordingly with IEC 62 040-3
Overload capability:	
• 10 min	115%
• 60 sec	135%

Battery	
Type	Lead Acid, sealed, free maintenance VRLA
Unit Capacity	Depending on backup time
Nominal UPS Battery Voltage	252 Volt DC
Battery charger type	PWM hi efficiency, one in each power module
Charging Cycle	Smart Charge technology 3-step advanced cycle
Max Charging Current	2,5 A each power module

Environmental specs	
Noise level @ 1m	<80 dBA
Working temperature range	from 0°C to +40°C
Stock temperature range	from -20°C to +50°C (excluded batteries)
Humidity range	0-95% not condensing
Protection degree	IP21

Mechanical an Miscellaneous	
Net Weight empty cabinet	256 + 610 kg
Net Weight power module	8,5 kg
Dimensions (WxHxD)	820 x 2050 x 750 + 1650 x 2050 x 750 (mm)
Colour	RAL 7016 / RAL 7035 (optional)
Technology rectifier/booster/inverter	IGBT
Communication Interface	2x RS232 port for service, 2x 5 Dry contacts 1x logic level port, N.2 SNMP slot
Input/Output connections	3Ph + N + PE
Number of Control boards	4
Number of installable Power Modules	up to 72 of 6,7 kW
Standards	EN 62040-1, EN 62040-2, EN 62040-3