

KEOR T 120 kVA

3 102 29



INDEX

Page

- 1. General specifications 1
- 2. Technical specifications 2

1. GENERAL SPECIFICATIONS

Legrand UPS model Keor-T 120 is an uninterruptible power source with 3-Level IGBT switching technology, high frequency PWM technology, Double Conversion On-line, solid neutral, with the possibility to have on site modular redundancy up to total 8 units, Rated Power 120 kVA – 108 kW.

Batteries are lead acid, sealed, free maintenance, valve regulated, and arranged in external battery cabinet.

1.1 Architecture

Legrand UPS model KEOR T 120 has stand-alone architecture.

UPS is composed by following parts;

- IGBT Rectifier/PFC
- 3-Level IGBT Switching Technology
- Digital Signal Processor (DSP)
- 3.5" TFT Touch Panel
- Automatic Bypass
- Dual Input Bypass
- Internal Manual Bypass
- Standard Internal Backfeed Protection
- Internal Battery Drawer Shelves

The UPS can be easily configured on site, by the authorized personnel, to operate in parallel. Also it is possible to arrange the dual bypass by removing bridge connection on each input phase.

Legrand Keor-T 120 has 3-Level IGBT switching technology and there is no transformer in the unit. These provide high efficiency for the unit.

Backfeed protection provides additional protection at the input in the event of bypass thyristors are short circuited.

By using internal backfeed contactor in bypass line provides safety when fault situation occurs in static bypass line and prevents upstream energy to the input.

The internal backfeed protection provides an easy on site installation without any additive cabling or special MCCB type in the upstream distribution panel

1.2 Redundancy:

The Redundancy of the UPS allows N+X redundant and power upgrade configurations. Parallel feature is standard at Keor-T 120. Up to 8 units of same size UPS can be connected in parallel.

1.3 By-pass

Keor T has internal both static bypass and mechanical (maintenance) bypass as standard. Addition to this input and bypass inputs can easily be separated to obtain dual input by removing the bridge on the connector.

1.4 Control and Monitoring:

Keor T is equipped with a touch screen graphic TFT display that provides information, measurements, statuses and alarms of the UPS in different languages. Below this display, there is a multicolour LED bar showing status of UPS.

- GREEN: Normal or ECO Mode Operation
- ORANGE: Bypass or Battery Operation
- RED: Load not Supplied

A dedicated software of remote monitoring and management, installed on a PC connected to the UPS, allows to check and set all working parameters of Keor T (the same functions available on the UPS control panel) and, furthermore, to schedule and program computer remote shutdown. Optional software (UPSMAN) or Net Interface card (CS121 SK) allow the multi server shutdown and UPS remote control on the LAN. Also, standard interface board comes with;

- RS232 Serial Communication Port
- Emergency Power Off (UPS OFF)
- Generator Contact (GEN ON)
- 4pcs programmable Dry Contact Information
- 2 contactor relays for Bypass and Battery
- ModBus (over RS485, with 2400 Baud Rate)

Standard Dry Contact Alarms are General Alarm, Bypass Active, Input Failure and Synchronization OK. Addition to these; High Temperature, Battery Test Failure, Output Failure alarms can be assigned to the contacts. Each alarm can be assigned to separate contacts but also one alarm may be assigned to all contacts.

Keor T front panel is controlled by DSP microprocessor which works together with DSP microprocessors in rectifier and inverter; by display is possible to check all measurements, working parameters and status of the system.

Here follow the measurements and working parameters available on the display:

RECTIFIER (INPUT)

- Voltage (Vac), per phase
- Current (Aac), per phase
- DC BUS Voltage (\pm Vdc)
- Heatsink Temperature ($^{\circ}$ C)

FREQUENCY

- Input Frequency (Hz)
- Output Frequency (Hz)

BATTERY

- Voltage (\pm Vdc)
- Current (\pm Adc)
- Temperature
- Autonomy (minute)

INVERTER (OUTPUT)

- Voltage (Vac), per phase
- Current (Aac), per phase
- Apparent Power (kVA), per phase
- Active Power (kW), per phase
- Power Factor (load), per phase
- Bypass Voltage, per phase
- Load (%), per phase
- Heatsink Temperature ($^{\circ}$ C)

1. GENERAL SPECIFICATIONS *(continue)*

The UPS allows also the following settings by **display**:

OUTPUT

Voltage (380/400/415)
Frequency (50Hz/60Hz)

PARALLEL MODE

Parallel Mode
(Enable/Disable(Single))
UPS ID

BATTERY

Battery String
Battery Capacity

Redundancy (+1, +2, ..., +7)
Operation Mode (Redundancy
Power Increase)

COMMAND MENU

Priority (Online (Inverter) /Green (Bypass))
Battery Test (KEOR T tests the battery automatically once each 90 days)
Maintenance (Rectifier, Inverter, Bypass, Load Supply – YES/NO)

RELAY FUNCTIONS

Relay 1 (General Alarm as default.)*
Relay 2 (Input Failure as default.)*
Relay 3 (Battery Failure as default.)*
Relay 4 (Output Failure as default.)*

(*) Relay output alarm information can be changed from front panel.

OPTIONS

Alarm Voice (Enable/Disable)
Key Voice (Enable/Disable)
Warning Window (Enable/Disable)

OTHER

Display Brightness (0 to 100)
Emergency Power Off (NC/NO)
Generator Mode (NC/NO)
ModBus ID
Time (hh:mm. Required for Event Log stamp)
Date (dd:mm:yyyy. Required for Event Log stamp)
Language (English)

Legrand Keor-T displays up to 500 last events. Events are stored in EEPROM using FIFO method. Order number of last occurred event is 001 and the last event in the list is erased when there are 500 events.

The UPS KEOR T has the CE Mark accordingly with the EU Directives 73/23, 93/68, 89/336, 92/31, 93/68 and it complies with following standards:

- EN 62040-1 "General rules for electric safety"
- EN 62040-2 "Electromagnetic compatibility and immunity (EMC)"
- EN 62040-3 "Performances and testing rules"

2. TECHNICAL SPECIFICATIONS

General Specifications	
UPS Topology	On line double conversion VFI SS 111
Architecture of the UPS	Stand alone, transformerless, On-Site Paralleling
In/Out phase Configuration	Three phase-Three phase
Neutral	Neutral Passing through
Switching Technology	3-Level IGBT
Backfeed Protection	Internal, standard
Output wave form on mains operation	Sinusoidal
Output wave form on battery operation	Sinusoidal
Standards	EN 62040-1, EN 62040-2, EN 62040-3

Input	
Nominal Voltage	400 V three phase + neutral + PE
Voltage Range	338 - 459 Ph-Ph full load 208 - 459 Ph-Ph half load
Frequency	45 - 65Hz
THDi	< 5% at full load
Power Factor	> 0.99

Bypass	
Nominal Voltage	380/400/415V
Voltage Range	-18% +15% (adjustable)
Frequency	47-53 (adjustable) or 57-63 (adjustable)
Bypass type	Static and electro-mechanic
Transfer time	Zero
Manual Bypass	Built-in

Output with mains (AC-AC)	
Nominal Voltage	380V, 400V, 415V three phase + neutral + PE
Nominal Power	120.000 VA
Active Power	108.000 W
Voltage variation (static)	± 1%
THDv on nominal power (linear load)	< 2%
THDv on nominal power (non-linear load)	< 4%
Frequency	50 Hz or 60 Hz (selectable)
Frequency tolerance	± 0,1% Synchronized with bypass frequency
Current Crest Factor	2,5:1 accordingly to IEC 62040-3
Overload capability:	
* 10min	125% load rate with no bypass transfer
* 1min	150% load rate with no bypass transfer

Output in battery Operation (DC-AC)	
Nominal Voltage	380V, 400V, 415V three phase + neutral + PE
Nominal Power	120.000 VA
Active Power	108.000 W
Voltage variation (static)	± 1%
THDv on nominal power (linear load)	< 2%
THDv on nominal power (non-linear load)	< 5%
Frequency	50 Hz or 60 Hz (selectable)
Frequency tolerance	± 0,01% free run
Current Crest Factor	2,5:1 accordingly to IEC 62040-3
Overload capability:	
* 10min	125%
* 1min"	150%

Battery	
Type	Lead Acid, sealed, maintenance free VRLA
Nominal UPS Battery Voltage	±360 Volt DC
Battery charger type	IGBT Rectifier also charges batteries
Charging Cycle	Intelligent with boost charge and advanced management
Max Charging Current without derating	8,0 A

Environmental specifications	
Noise level @ 1m	< 57dBA
Operating temperature range	from 0°C to +40°C
Stock temperature range	from -20°C to +50°C
Humidity range	20-95% not condensing
Protection degree	IP20

Mechanical and Miscellaneous	
Net Weight	365 kg
Dimensions (WxHxD)	800 x 1650 x 800 mm
Colour	Enclosure: RAL 7016 Front Door Metal: RAL 9005
Communication Interface	1 serial port RS232, 1 RS485, 1 smart port for internal SNMP, 4 Dry Contacts, 1 EPO, 1 GENSET
Input/Output connections	3P + N + PE
Input/Output Circuit Breaker	250A/250A